

WaterHog Silver Mat



WaterHog Silver mats feature the unique bi-level design that made WaterHog mats famous, with a new antimicrobial surface that reduces bacteria growth by 99%!

•

•

•

•

•

•

•

WaterHog Silver features a zirconium phosphate-based ceramic ion-exchange resin that contains

WaterHog Silver Mat

silver
.
This
resin
is eff
ectiv
e ag
ainst
a bro
ad s
pectr
um
of mi
croor
gani
sms
that
caus
e dis
color
ation
,
odor,
biofo
uling
, and
other
aest
hetic
probl
ems.
In in
depe
nden
t
tests
cond
ucte
d by
The
Micr
oSta

r
Lab,
Wate
rHog
Silve
r red
uced
bact
eria
grow
th by
more
than
99%.
Duri
ng te
sting
, Wat
erHo
g Sil
ver
mat
swat
ches
are p
lace
d in
a ste
rile c
ontai
ner, i
nocu
lated
with
bact
eria[^]
, and
incu
bate
d for
a sp
ecifie



WaterHog Silver Mat

d
time.
After
incu
batio
n, co
lonie
s of r
ecov
ered
bact
eria
are c
ount
ed
and
used
to de
termi
ne p
erce
nt re
ducti
ons.
In
the
Wate
rHog
Silve
r
test,
less
than
1%
of
the b
acter
ia re
main
ed;
more
than

99%
had
been
redu
ced.

^Spe
cifica
lly
the k
lebsi
ella
pneu
moni
ae
and
stap
hyloc
occu
saur
eus
bact
eria

Plea
se
note,
mat
sizes
are a
ppro
xima
te as
rubb
er sh
rinks
and
expa
nds
in co
njun
ction

WaterHog Silver Mat

with temperature and time. Tolerable manufacturing size variance is 3-5%.

Specifications

SURFACE
Material: Solution-dyed PET (polyethylene terephthalate) featuring zirconium phosphate

ate-based ceramic ion-exchange resin containing silver. Weight: 30 ounces/sq yd
Construction: Needle-punched
Design: Honeycomb

BACKING
GOPTIONS
Material: SBR rubber – smooth

WaterHog Silver Mat

oth
or un
ivers
al cle
ated
Thic
knes
s: 78
-mil (body
thick
ness
78-m
il; bo
rder t
hickn
ess
143-
mil)

OVE
RAL
L
MAT
THIC
KNE
SS:
3/8
inch
(0.37
5?)

STA
NDA
RDS
& TE
STIN
G

Certi
fied
high-

tracti
on
by
the
Natio
nal
Floor
Safet
y Ins
titute
(NFS
I)
Pass
es C
PSC
FF
1-70
for
the s
urfac
e fla
mma
bility
of ca
rpets

Clea ning Instr ucti ons

For
the
best
resul
ts, ut
ilize
the f
ollow
ing cl
eani



WaterHog Silver Mat

ng m
etho
d to
clea
n
your
Wate
rHog
mat:

Vacu
um r
egul
arly (
daily
in hi
gh-tr
affic
com
merc
ial ar
eas;
week
ly in l
ower
traffi
c are
as).
Extra
ct or
hose
off
as n
eede
d to r
emo
ve h
eavy
soil/d
ebris
. Ha
ng

mat
to
dry.
Alwa
ys m
ake
sure
the
mat
is
dry b
efore
placi
ng it
back
in se
vice
.

**Stan
dard
Size
s (A
ppro
xima
te)**

SQQ
izyty
e . .
1 6
- +
5
2'
X
3'
4 4
9 7
. .



WaterHog Silver Mat

SQQ
iztyty
e . .
16
- +
5
94
5

SQQ
iztyty
e . .
16
- +
5
3'
X
5'
11
21
48
. .
97
50
4'
X
6'
11
87
45
. .
97
50
3'
X
1
0'22
21
98
. .
94
55
6'
X
8'
44
42
75
. .
95



WaterHog Silver Mat

SQQ
iztyty
e . .
16
- +
5
55

SQQ
iztyty
e . .
16
- +
5



FLOORMAT.COM
products with purpose.